



LUMAX 2.0

Offers the esthetics of traditional e.Max with the strength of zirconia!

Choose LuMax to create a look for your patient that is Luminous to the max!



LuMax from Pittman Dental Laboratory offers the esthetics of traditional e.Max® but with increased flexural strength!

LuMax has a flexural strength of 765 MPa!

Traditional lithium disilicate restorations have a flexural strength of no more than 400 MPa.

Indications	Recommended Process	Recommended Product
Single Anterior and Posterior Crowns	Dual Cure Resin	Panavia SA Plus*
Implant Restorations	Dual Cure Resin	Panavia SA Plus*
Inlays & Onlays	Dual Cure Resin	Panavia SA Plus or Clearfil Esthetic EX*

* **kuraray**